

New equipment report



POWER-MIX MODEL L46

- **Strong vibrating Action**, for test tubes 7 mm diam. up to 35 mm
- Both, "Press-to-Mix" action and "continuous" action are provided
- Stepless speedcontrol, up to maximum speed 2500 rpm
- Strong and steady unit
- Lined out for accessory adaption as described below
- Supplied with line-cord and standard cup
- Voltage requirements 230 Volts 50/60 Hz.
115 Volts 50/60 Hz.
- Powerconsumption 40 Watts
- Dimensions: 135 x 120 x 135mm (LxDxH)
- Weight: 3,2 kg

ORDERING: CAT.NO. 46000 (220V50/60Hz)
46010 (115V50/60Hz)

A COMPLETE MIXER-LINE FROM ONE BASIC UNIT



Order basic model L46 together with additional accessories below



A COMPLETE MIXER-LINE FROM ONE BASIS UNIT

- | | |
|---|--|
| <p>A MICRO-TITRE-PLATE-HOLDER</p> <p>Ordering number 46100</p> | <p>easy adaptable holder for one 96-well micro-titre-plate shaking with Model L46</p> |
| <p>B MINI-REACTION-TUBE-HOLDER</p> <p>Ordering number 46200</p> | <p>easy adaptable holder for 20 mini-reaction-tubes; including polythene-foam holder</p> |
| <p>b1 Spare polythene-foam-holder for 20 mini-reacton-tubes</p> <p>Ordering number 46250</p> | |
| <p>C One-position TEST-TUBE-HOLDER</p> <p>Ordering number 46300</p> | <p>easy adaptable holder for a single test-tube (max. 20x200 mm) including aluminum rod (M10)</p> |
| <p>D Multi-position TEST-TUBE-HOLDER</p> <p>Ordering number 46400</p> | <p>easy adaptable holder for up to 7 test-tubes (18x115mm) (max) Changing while mixing is possible</p> |
| <p>E Universal CONTACT-PLATE</p> <p>Ordering number 46500</p> | <p>easy adaptable universal contact-plate for touching and mixing up to 6 tubes at once</p> |